

# 810010100/DB | B-144-LN-8W-M12NS/15G/AJ



Fiber OSP cable, LightScope ZWP® Blown Micro Single Jacket, 144 fiber, All-Dielectric Stranded Loose Tube Arid-Core® Construction, Gel-filled, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	B-LN


## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	0
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Laser
<b>Jacket Marking Text</b>	Unified National Networks (UNN),(METER MARK), COMMSCOPE, 144 CORE SM G652D, HDPE,(DATE OF MANUFACTURE) (SERIAL NUMBER)
<b>Subunit, quantity</b>	12
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	144

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	1.45 mm   0.057 in
<b>Diameter Over Jacket</b>	8.4 mm   0.331 in

## Representative Image



## Material Specifications

**Jacket Material** High density polyethylene (HDPE)

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	126 mm   4.961 in
<b>Minimum Bend Radius, unloaded</b>	84 mm   3.307 in
<b>Tensile Load, long term, maximum</b>	469 N   105.435 lbf
<b>Tensile Load, short term, maximum</b>	1566 N   352.051 lbf
<b>Compression</b>	10 N/mm   57.101 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Flex</b>	25 cycles
<b>Flex Test Method</b>	IEC 60794-1 E6
<b>Impact</b>	0.3 N-m   2.655 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1-21 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1-21 E7
<b>Vertical Rise, maximum</b>	769 m   2,522.966 ft

## Optical Specifications

# 810010100/DB | B-144-LN-8W-M12NS/15G/AJ

**Fiber Type** G.652.D | G.652.D and G.657.A1

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Storage Temperature</b>	-30 °C to +75 °C (-22 °F to +167 °F)
<b>Cable Qualification Standards</b>	IEC 60794-5-10
<b>Environmental Space</b>	Air-blown, microduct
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F4

## Environmental Test Specifications

<b>Cable Freeze</b>	-2 °C   28.4 °F
<b>Cable Freeze Test Method</b>	IEC 60794-1 F15
<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	IEC 60794-1-21 E14
<b>Heat Age</b>	-30 °C to +85 °C (-22 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1-22 F9
<b>Low High Bend</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Low High Bend Test Method</b>	IEC 60794-1-21 E11
<b>Temperature Cycle</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1

## Packaging and Weights

**Cable weight** 63 kg/km | 42.334 lb/kft

## Included Products

DB-8W-LT – LightScope ZWP® Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable