

R-360B-R1VB



2 Port omni antenna, 2x 694–960 MHz, 360° HPBW, 1x RET

- Single antenna provides for 2xMIMO and Rx diversity service
- Simplifies infrastructure and space requirements compared to traditional V-pol antennas
- Ideal solution for rural coverage

General Specifications

Antenna Type	Omni
Band	Single band
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	ASA, UV resistant
Radiator Material	Aluminum Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, low band	2
RF Connector Quantity, total	2

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Male
Input Voltage	10–30 Vdc
Internal RET	Low band (1)
Power Consumption, active state, maximum	10 W
Power Consumption, idle state, maximum	2 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

Length	1999 mm 78.701 in
Net Weight, without mounting kit	22.6 kg 49.824 lb

R-360B-R1VB

Outer Diameter

305 mm | 12.008 in

Port Configuration



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	300 W

Electrical Specifications

Frequency Band, MHz	694–790	790–890	890–960
Gain, dBi	10.4	11	11.4
Beamwidth, Horizontal, degrees	360	360	360
Beamwidth, Vertical, degrees	13.2	11.7	10.5
Beam Tilt, degrees	2–14	2–14	2–14
USLS (First Lobe), dB	20	19	19
Isolation, Cross Polarization, dB	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150

R-360B-R1VB

Input Power per Port, maximum, watts	250	250	250
---	-----	-----	-----

Electrical Specifications, BASTA

Frequency Band, MHz	694–790	790–890	890–960
Gain by all Beam Tilts, average, dBi	10.1	10.7	11
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.6	±0.7
Beamwidth, Vertical Tolerance, degrees	±0.8	±1	±0.8
CPR at Boresight, dB	16	17	19

Mechanical Specifications

Wind Loading @ Velocity, frontal	376.0 N @ 150 km/h (84.5 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	376.0 N @ 150 km/h (84.5 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	376.0 N @ 150 km/h (84.5 lbf @ 150 km/h)
Wind Speed, maximum	200 km/h (124 mph)

Packaging and Weights

Width, packed	420 mm 16.535 in
Depth, packed	400 mm 15.748 in
Length, packed	2265 mm 89.173 in
Weight, gross	29 kg 63.934 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---