

Fiber indoor cable, LazrSPEED® Riser/LSZH rated, MPO Trunk, interlocking aluminum armored, Multimode OM4, 144 fiber multi-unit with 12 fiber subunits, Gel-free, Feet jacket marking, Aqua jacket color

## Product Classification

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®                                                          |
| <b>Product Type</b>          | Fiber indoor cable                                                  |
| <b>Product Series</b>        | N-MZ                                                                |


## General Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Armor Type</b>                   | Interlocking aluminum |
| <b>Cable Type</b>                   | MPO trunk cable       |
| <b>Construction Type</b>            | Armored               |
| <b>Subunit Type</b>                 | Gel-free              |
| <b>Jacket Color</b>                 | Aqua                  |
| <b>Jacket Marking</b>               | Feet                  |
| <b>Subunit, quantity</b>            | 12                    |
| <b>Fibers per Subunit, quantity</b> | 12                    |
| <b>Total Fiber Count</b>            | 144                   |

## Dimensions

|                                     |                     |
|-------------------------------------|---------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 3 mm   0.118 in     |
| <b>Diameter Over Armor</b>          | 20.96 mm   0.825 in |
| <b>Diameter Over Jacket</b>         | 23 mm   0.906 in    |

## Representative Image



## Mechanical Specifications

|                                          |                                       |
|------------------------------------------|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 345 mm   13.583 in                    |
| <b>Minimum Bend Radius, unloaded</b>     | 230 mm   9.055 in                     |
| <b>Tensile Load, long term, maximum</b>  | 400 N   89.924 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 1335 N   300.12 lbf                   |
| <b>Compression</b>                       | 85 N/mm   485.363 lb/in               |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 300 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 35 N-m   309.776 in lb                |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 112 m   367.454 ft                    |

## Optical Specifications

|                   |                                           |
|-------------------|-------------------------------------------|
| <b>Fiber Type</b> | OM4, LazrSPEED® 550   OM4, LazrSPEED® 550 |
|-------------------|-------------------------------------------|

## Environmental Specifications

|                                 |                                      |
|---------------------------------|--------------------------------------|
| <b>Installation temperature</b> | -20 °C to +60 °C (-4 °F to +140 °F)  |
| <b>Operating Temperature</b>    | -20 °C to +70 °C (-4 °F to +158 °F)  |
| <b>Storage Temperature</b>      | -40 °C to +70 °C (-40 °F to +158 °F) |

# 760120105 | N-144-MZ-5K-F12AQ

|                                      |                                                             |
|--------------------------------------|-------------------------------------------------------------|
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-83-596   Telcordia GR-409                       |
| <b>Environmental Space</b>           | Low Smoke Zero Halogen (LSZH)   Riser                       |
| <b>Flame Test Listing</b>            | NEC OFCR-ST1 (ETL) and c(ETL)                               |
| <b>Flame Test Method</b>             | IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685 |

## Environmental Test Specifications

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| <b>Heat Age</b>                      | -20 °C to +85 °C (-4 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                      |
| <b>Low High Bend</b>                 | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11           |
| <b>Temperature Cycle</b>             | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1             |

## Packaging and Weights

|                     |                            |
|---------------------|----------------------------|
| <b>Cable weight</b> | 366 kg/km   245.941 lb/kft |
|---------------------|----------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>                                                                                                          |
|---------------|--------------------------------------------------------------------------------------------------------------------------------|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available                                                                 |
| CHINA-ROHS    | Below maximum concentration value                                                                                              |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system                                                 |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant                                                                                                                      |
| UK-ROHS       | Compliant                                                                                                                      |



## Included Products

|          |                                                       |
|----------|-------------------------------------------------------|
| CS-5K-MP | – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber |
|----------|-------------------------------------------------------|

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable