# UGVQXUCT8

#### **Base Product**



Ultra Low Loss (ULL) OM5 MPO8 (Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 8-Fiber, Plenum

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity

Color, boot A Gray

Color, connector A Lime green

Connector B, quantity

Construction Type Stranded
Furcation Color Lime green

Interface, Connector A MPO-08/UPC Male

Interface, Connector B Unterminated

Jacket Color Lime green

**Polarity** Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 8

**Dimensions** 

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305

Page 1 of 8




# UGVQXUCT8

Cable Assembly Length Range (ft)

10 - 999

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$ 

**Optical Specifications** 

Fiber Mode Multimode

**Fiber Type** OM5, LazrSPEED®

### **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

# Agency Classification ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



### Included Products

760248188 – Fiber indoor cable, LazrSPEED® Plenum for MPO Trunks, 8 fiber, Multimode OM5, Feet jacket

Page 2 of 8


# UGVQXUCT8

P-008-MP-5G-F08LM/20T 860659020 marking, Aqua jacket color

MPO-08, ULTRA LOW LOSS, MALE, OM5, LIME-GREEN, 2mm



# 760248188 | P-008-MP-5G-F08LM/20T



Fiber indoor cable, LazrSPEED® Plenum for MPO Trunks, 8 fiber, Multimode OM5, Feet jacket marking, Aqua jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit Type Gel-free

Jacket Color Aqua

Jacket Marking Feet

Total Fiber Count


Dimensions

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket5.2 mm | 0.205 in

Representative Image



# 760248188 | P-008-MP-5G-F08LM/20T



### Mechanical Specifications

Minimum Bend Radius, loaded 79 mm | 3.11 in

Minimum Bend Radius, unloaded 52 mm | 2.047 in

**Tensile Load, long term, maximum** 133 N | 29.9 lbf

**Tensile Load, short term, maximum** 445 N | 100.04 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 417 m | 1,368.11 ft

Optical Specifications

**Fiber Type** OM5, LazrSPEED® wideband

**Environmental Specifications** 

**Installation temperature**  $0 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

Page 5 of 8



# 760248188 | P-008-MP-5G-F08LM/20T

**Operating Temperature**  $0 \, ^{\circ}\text{C to } +70 \, ^{\circ}\text{C (} +32 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)
Flame Test Method NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 33 kg/km | 22.175 lb/kft

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



# 860659020



### MPO-08, ULTRA LOW LOSS, MALE, OM5, LIME-GREEN, 2mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface Feature Pinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

**COMMSCOPE®** 

# 860659020

#### **Packaging quantity**

1

# Regulatory Compliance/Certifications

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed u

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Agency