


SFG22HD-10-3-126



G22HD High Capacity Sector Frame with 2 7/8in OD x 10.5ft face.
Includes three 2 3/8in OD x 126in antenna pipes.

Product Classification

| | |
|------------------------------|---|
| Regional Availability | North America |
| Portfolio | CommScope® |
| Product Type | High capacity Tower sector frame |
| Product Series | G2 |
| Ordering Note | CommScope® standard product in the United States and Canada |
| Warranty | One year |

General Specifications

| | |
|--------------------------|--|
| Application | 4G LTE antenna/radio mount |
| Mounting | Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD |
| Patent Number | Patent pending |
| Pipe, quantity | 3 |
| Sectors, quantity | 1 |
| Tower Taper | Non-tapered Tapered |

Dimensions

| | |
|-----------------------------------|----------------------|
| Height | 3,200.4 mm 126 in |
| Face Width | 3.2 m 10.5 ft |
| Width | 3,200.4 mm 126 in |
| Pipe Length | 3,200.4 mm 126 in |
| Face Support Pipe Diameter | 73.025 mm 2.875 in |
| Mounting Diameter, maximum | 218.44 mm 8.6 in |
| Mounting Diameter, minimum | 38.1 mm 1.5 in |
| Pipe Outer Diameter | 60.325 mm 2.375 in |
| Stand-off Distance | 1,041.4 mm 41 in |

Material Specifications

SFG22HD-10-3-126

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Frame | Pipe mounts | Plain end pipes (3) | Stiff arms (2) | Tower attachment

Packaging quantity 1

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code