


NG4-VSMRF28 | NG4 VAM, 2 1X8 SPLITTERS, LC /APC, RIGHT



NG4access® Module VAM, Splitter, 1x8, symmetrical split, singlemode, LC /APC, front, right, 2 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand China EMEA India Latin America North America |
| Portfolio | CommScope® |
| Product Type | Splitter module |
| Product Brand | NG4access® |
| Product Series | FACT NG4 |

General Specifications

| | |
|--------------------|--------------------------------|
| Device Type | Plug-and-play module |
| Functionality | Splitting |
| Technology Type | Planar lightwave circuit (PLC) |
| Access | Front |
| Application | For use with NG4 access frames |
| Distribution Type | 1 x 8 splitter (2) |
| Interface, front | LC/APC |
| Interface, Input | LC/APC |
| Interface, Output | LC/APC |
| Split Ratio | Symmetrical |
| Splitter, quantity | 2 |
| Tray Orientation | Right orientation |

Dimensions

| | |
|--------|---------------------|
| Height | 13.21 mm 0.52 in |
| Width | 159.77 mm 6.29 in |

NG4-VSMRF28 | NG4 VAM, 2 1X8 SPLITTERS, LC /APC, RIGHT

Depth 130.3 mm | 5.13 in

Optical Specifications

| | |
|---|-------------------------|
| Directivity, minimum | 55 dB |
| Performance Grade | Grade O (PLC, low loss) |
| Polarization Dependent Loss, maximum | 0.2 dB |
| Uniformity, maximum | 1.4 dB |
| Wavelength Range | 1260–1625 nm |
| Insertion Loss, Splitter, maximum | 10.8 dB |
| Return Loss, Connector, minimum | 55 dB |

Packaging and Weights

Packaging quantity 1