

16-port, low band diplexed antenna, 2x 698-728 MHz, 2x758-798 MHz, 2 x 698-798 MHz, 2 x 824-894 MHz and 8 x 1695-2360 MHz, 65° HPBW, 6 x RET

- Features broadband Low Band (698-894 MHz) and Mid Band (1695-2360 MHz) arrays for 4T4R (4X MIMO) capability for 700 and 850 MHz, AWS, PCS and WCS applications
- Both Low Band arrays are diplexed for independent tilt, with one array providing two ports of B29 and two ports of B14 and the other array providing two ports of B14 and two ports of B5
- Excellent wind loading characteristics
- Optimized SPR performance across all operating bands

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	8
RF Connector Quantity, low band	8
RF Connector Quantity, total	16

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	2 female 2 male
Input Voltage	10-30 Vdc
Internal RET	Low band (4) Mid band (2)
Power Consumption, active state, maximum	8 W
Power Consumption, idle state, maximum	1 W

Page 1 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 8, 2024




J3AH4-65B-R6

Protocol

Dimensions

Width	498 mm 19.606 in
Depth	197 mm 7.756 in
Length	1828 mm 71.969 in
Net Weight, antenna only	43.6 kg 96.121 lb

Array Layout



R4	Array ID	Frequency (MHz)	RF Connector	RET (MRET)	AISG No.	AISG RET UID
	R1	698-728	1 - 2	1	AISG1	CPxxxxxxxxxxxXMM.1
	R2	758-798	3 - 4	2	AISG1	CPxxxxxxxxxxxXMM.2
	R3	698-798	5 - 6	3	AISG1	CPxxxxxxxxxxxXMM.3
	R4	824-894	7 - 8	4	AISG1	CPxxxxxxxxxxXMM.4
	¥1	1695-2360	9 - 10	5	AISG1	CPxxxxxxxxxxxXMM.5
	¥2	1695-2360	11 - 12	5	AISGT	CPXXXXXXXXXXXXXXXXIVIM.:
	Y3	1695-2360	13 - 14	6	AISG1	CPxxxxxxxxxxxXMM.6
	¥4	1695-2360	15 - 16	0	AISGT	

Port Configuration



Page 2 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 8, 2024



3GPP/AISG 2.0 (Multi-RET)

J3AH4-65B-R6

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 - 2360 MHz 698 - 798 MHz 824 - 894 MHz
Polarization	±45°
Total Input Power, maximum	1,280 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	698-798	824-896	1695-1880	1850-1990	1920-2180	2300-2360
Beamwidth, Horizontal, degrees	64	61	70	67	62	60
Beamwidth, Vertical, degrees	12.1	11	7	6.4	6.1	5.5
Beam Tilt, degrees	2-14	2-14	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	15	18	17	18	18	18
Front-to-Back Ratio at 180°, dB	31	29	34	34	33	35
Front-to-Back Total Power at 180° ± 30°, dB	24	24	28	27	27	28
Isolation, Cross Polarization, dB	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	150	150	250	250	250	200

Electrical Specifications, BASTA

Frequency Band, MHz	698-798	824-896	1695-1880	1850-1990	1920-2180	2300-2360
Gain by all Beam Tilts, average, dBi	13.6	14.4	16.1	16.8	17.3	17.7
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.3	±0.8	±0.8	±0.8	±0.6
Beamwidth, Horizontal Tolerance, degrees	±9.9	±6.3	±7.8	±10.3	±5.8	±4.3
Beamwidth, Vertical Tolerance, degrees	±0.9	±0.6	±0.4	±0.3	±0.4	±0.2
USLS, beampeak to 20° above beampeak, dB	15	17	12	14	12	11
CPR at Boresight, dB	23	26	21	22	23	22

Page 3 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 8, 2024



<u>J3AH4-65B-R6</u>

CPR at Sector, dB	11	9	6	5	5	6	
Mechanical Spe	cifications						
Wind Loading @ Velocity	/, frontal	622	.0 N @ 150 km/h (1	39.8 lbf @ 150) km/h)		
Wind Loading @ Velocity	r, lateral	188	.0 N @ 150 km/h (4	12.3 lbf @ 150	km/h)		
Wind Loading @ Velocity	, maximum	746	746.0 N @ 150 km/h (167.7 lbf @ 150 km/h)				
Wind Loading @ Velocity	/, rear	428	.0 N @ 150 km/h (9	96.2 lbf @ 150	km/h)		
Wind Speed, maximum		241	km/h (150 mph)				
Packaging and \	Neights						
Width, packed		565	mm 22.244 in				
Depth, packed		309	mm 12.165 in				
Length, packed		201	5 mm 79.331 in				
Weight, gross		57.4	4 kg 126.545 lb				
Regulatory Com	Regulatory Compliance/Certifications						
Agency	Classification						
ISO 9001:2015	Designed, manufa	ctured and/or	distributed under th	is quality man	agement system		
Included Produc BSAMNT-4		le Profile Anter	ina Downtilt Mounti	ing Kit for 2.4 -	4.5 in (60 - 115 r	nm) OD round members.	
			cissor top bracket s	-	,	-	
* Footnotes							
Performance Note	Severe environm	ental conditio	ns may degrade c	ptimum perfo	ormance		

Page 4 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 8, 2024



BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification	
Product Type	Downtilt mounting kit
General Specifications	
Application	Outdoor
Color	Silver
Dimensions	
Compatible Diameter, maximum	115 mm 4.528 in
Compatible Diameter, minimum	60 mm 2.362 in
Weight, net	6.5 kg 14.33 lb
Material Specifications	
Material Type	Galvanized steel
Packaging and Weights	
Included	Brackets Hardware
Packaging quantity	1
Pequilatory Compliance/	

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 5 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 10, 2024

