

G2-MODULES



G2 Modules fit into any AGL, G2 EPX, HD or UD panels offering density from 96f LC to 144f LC (UD) per RU adding flexibility to any configuration

- Available in standard loss and ultra-low loss (ULL) configurations
- Internal shutters on LC modules reduces dust contamination, automatically actuates with connector insertion or removal and the shutter door illuminates with VFL when checking continuity
- Polarity configurations to support any application in either Method B Enhanced, Method B or Method A

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	G2

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL

Packaging and Weights

Packaging quantity	1
---------------------------	---