
FDH1204-48SE2



HELIAX® Direct-connect 6×24 hybrid trunk assembly: 6 pairs of 4AWG DC conductors $\times 24$ pairs of single mode fibers.

- RRU (top) breakout; 6 blunt-cut power cords (6-6AWG pairs), 48 single mode fibers in outdoorrated tails with ODC-compatible interface
- BBU (bottom) breakout; 12-4AWG power conductors blunt cut, 48 single mode fibers within 24 DLC tails

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Hybrid cable assembly

Product Brand HELIAX®

Product Series FDH

General Specifications

Conductors, quantity 12

Construction Type Direct breakout trunk

 Interface, Connector A
 ODC-LC

 Interface Feature, connector A
 Outdoor

 Interface Body Style, connector A
 Straight

and and a support of the support of

Interface Feature, connector B Standard

Interface Body Style, connector BStraightJacket ColorBlack

Total Fibers, quantity 48

Dimensions

Interface, Connector B

Cable Assembly Length Range (m) 10 - 130

Diameter Over Jacket 44.78 mm | 1.763 in

Center Conductor Gauge 4 AWG

Mechanical Specifications

Minimum Bend Radius 523.2 mm | 20.598 in Minimum Bend Radius, furcation 30 mm | 1.181 in

ANDREW® an Amphenol company

Page 1 of 2

DI C

FDH1204-48SE2

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2/B2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.75

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Packaging and Weights

Cable weight 3.4 kg/m | 2.285 lb/ft

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

