

CT-460-100



Cable Tie, Heat Stabilized, Weather-resistant, 460 mm length, 100 pcs

OBSOLETE

Replaced By:

CB-12-18LH

Heat-stabilized weather resistant acetal cable banding, 1/2 in x 18 in length with attached locking head, package contains 100 pieces

Product Classification

Product Type	Cable tie
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product in the United States and Canada

General Specifications

Accessories	Adapters
Color	Black
Hanger Type	Cable tie
Mounting	Angle member Cable ladder Round member

Dimensions

Height	1.778 mm 0.07 in
Width	7.112 mm 0.28 in
Length	0.46 m 1.51 ft
Compatible Diameter, maximum	127 mm 5 in
Compatible Diameter, minimum	4.775 mm 0.188 in

Material Specifications

Material Type	Heat-stabilized weather resistant nylon
----------------------	---

Mechanical Specifications

Tensile Force	533.786 N 120 lbf
----------------------	---------------------

CT-460-100

Environmental Specifications

Operating Temperature -60 °C to +115 °C (-76 °F to +239 °F)

Packaging and Weights

Packaging quantity 100

Weight, gross 0.54 kg | 1.19 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
CSA	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

