



Outside Plant Fiber Optic Cable, armored, 8-fiber, Singlemode, OS2, loose tube, gel-filled, 1000 m

OBSOLETE

This product was discontinued on: October 30, 2022

Replaced By:

760252030 Fiber OSP cable, PE, Gel-filled Central Tube, CST, 8 fiber, Singlemode G.652.D and G.657.A1,
O-008-CA-8Z-M08BK/28G/093 Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Asia
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LA

General Specifications

Armor Type	Corrugated steel
Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Fibers per Subunit, quantity	8
Total Fiber Count	8

Dimensions

Cable Length	1000 m 3,280.84 ft
Diameter Over Jacket	10.3 mm 0.406 in

Mechanical Specifications

1-1427433-4

Minimum Bend Radius, loaded	206 mm 8.11 in
Tensile Load, long term, maximum	890 N 200.08 lbf
Tensile Load, short term, maximum	2700 N 606.984 lbf
Flex	25 cycles

Optical Specifications

Fiber Type	OS2
-------------------	-----

Optical Specifications, Wavelength Specific

Standards Compliance	ANSI/TIA-568.A TIA-492CAAB (OS2)
-----------------------------	------------------------------------

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Cable weight	108 kg/km 72.573 lb/kft
---------------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable