

# 760254041 | EPX-1U-CHD-ENC



EPX 1U sliding panel, accepts (8) CHD style modules, adapter packs, or splice cassettes, providing up to 48 duplex LC ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel   Fiber patch/splice panel
<b>Product Series</b>	EPX

## General Specifications

<b>Application</b>	Accepts eight CHD modular cassettes   Accepts four G2 modular cassettes
<b>Color</b>	Black
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Module/Adapter Pack Slots, quantity</b>	4
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Total Fibers, quantity</b>	96
<b>Total Ports, quantity</b>	0

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	412.75 mm   16.25 in

## Environmental Specifications

<b>Safety Standard</b>	CSA 22.2   UL 1863
------------------------	--------------------

## Packaging and Weights

# 760254041 | EPX-1U-CHD-ENC

---

**Packaging quantity** 1  
**Weight, net** 3.529 kg | 7.78 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

