MC-CP14M-12-126



3-Sector Monopole Co-location Platform Kit, 12 in to 50 in OD, 14 ft 6 in face, includes twelve 126 in pipes

Product Classification

Product Type Co-location platform

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

Dimensions

Height 3,200.4 mm | 126 in

Face Width 4.42 m | 14.5 ft

Width 4,419.6 mm | 174 in

Pipe Length 3,200.4 mm | 126 in

Mounting Diameter, maximum1270 mm | 50 inMounting Diameter, minimum304.8 mm | 12 inPipe Outer Diameter60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Test Method TIA/EIA-222

Packaging and Weights



MC-CP14M-12-126

Included Plain end pipes (12) | Platform | Rail | Ring mount

Packaging quantity 1

Weight, net 831.027 kg | 1,832.1 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

