

MC-PK8-C



Low-Profile Co-location Platform Kit, 8 ft face, 12 in to 38 in OD, (9) 2-3 /8" OD x 72" Pipes, with Support Rail Kit

Please contact CommScope for detailed drawings prior to ordering.

Product Classification

Product Type	Monopole platform kit
Ordering Note	NSTD445 Compliant

General Specifications

Mounting	Monopole, 305–965 mm (12–38 in) OD
Pipe, quantity	9
Sectors, quantity	3

Dimensions

Height	1,828.8 mm 72 in
Face Width	2.438 m 8 ft
Width	2,438.4 mm 96 in
Pipe Length	1,828.8 mm 72 in
Face Support Pipe Diameter	88.9 mm 3.5 in
Mounting Diameter, maximum	965.2 mm 38 in
Mounting Diameter, minimum	304.8 mm 12 in
Pipe Outer Diameter	60.325 mm 2.375 in
Stand-off Distance	914.4 mm 36 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

MC-PK8-C

Environmental Specifications

EPA with 1/2 in (12 mm) radial ice 1.421 m² | 15.3 ft²

EPA without ice 1.533 m² | 16.5 ft²

Packaging and Weights

Included Hardware | Plain end pipes (9) | Platform | Rail | Ring mount

Packaging quantity 1

Weight, net 622.782 kg | 1373 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

EPA with 1/2 in (12 mm) radial ice EPA—Effective Projected Area

EPA without ice EPA—Effective Projected Area