

TC-96353-IP · Rev A · January 2023

EPX SPLICE PANEL

Product Description

The EPX Splice panel

(760254513 | EPX-3U-SPL-ENC) is a 3RU, 19-inch rack-mount panel that holds and protects splices when mating two blunt cables. Each panel accommodates up to 336 single fibers in 7 AGL splice trays (760241378 | AGL Splice-48). Each splice trays holds 48 fibers, each providing stackable, 48-fiber capacity per tray for a total of 336 single fiber splices. Accessories listed at right must be ordered separately.


PARTS LIST	
DESCRIPTION	QUANTITY
EPX SPLICE PANEL	1
RACK SCREW	4
TOOLS REQUIRED	
DESCRIPTION	QUANTITY
PHILLIPS #2 SCREWDRIVER	1
SNIPS	1
ACCESSORIES	
CABLE CLAMP	
MESH TUBING	
AGL SPLICE TRAY (760241378/AGL-Splice-48)	


Quick

Start


3

1






Install Cable as follows: (a) remove back cover (unscrew knob to release it); (b) route cable bundles to the rear of the panel; secure on cable mount using cable tie and felt tape; (c) bring bundles forward to the panel front; (d) unpack splice tray and identify components; (e) route bundles to splice tray for splicing on nearby table; (f) splice as shown; see Note below.




RIGHT REAR ENTRY



© 2023, CommScope, Inc. All Rights Reserved.

with splice tray.



-

28004-A

© 2023, CommScope, Inc. All Rights Reserved.