

CS44ZB2 Category 6A, F/UTP Cable, low smoke zero halogen, white jacket,4 pair count, 1000 ft (305 m) length reel

#### **Product Classification**

Regional Availability China

Portfolio NETCONNECT®
Product Type Twisted pair cable

General Specifications

**Product Number** CS44ZB

ANSI/TIA Category 6A

Cable Component Type Horizontal

**Cable Type** F/UTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Drain Wire TypeSolidJacket ColorWhite

Pairs, quantity 4

Separator Type Isolator

**Transmission Standards**ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

**Dimensions** 


Cable Length304.8 m | 1000 ftDiameter Over Insulated Conductor1.14 mm | 0.045 inDiameter Over Jacket, nominal7.188 mm | 0.283 in

Conductor Gauge, singles23 AWGDrain Wire Gauge26 AWG

**COMMSCOPE®** 

## 884032708/10

### Cross Section Drawing



### **Electrical Specifications**

Characteristic Impedance 100 ohm

**Characteristic Impedance Tolerance** ±15 ohm

**dc Resistance, maximum** 6.66 ohms/100 m | 2.03 ohms/100 ft

**Delay Skew, maximum** 45 ns

**Dielectric Strength, minimum** 1500 Vac | 2500 Vdc

Mutual Capacitance at Frequency 5.6 nF/100 m @ 500 MHz

Nominal Velocity of Propagation (NVP) 64 %

Operating Voltage, maximum 80 V

**Remote Powering**Fully complies with the recommendations set forth by IEEE 802.3 bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1,

CENELEC EN 50174-2 or TIA TSB-184-A

Segregation Class c

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Shield (Tape) Material Aluminum/Polyester

Mechanical Specifications

Pulling Tension, maximum 10.206 kg | 22.5 lb

**COMMSCOPE®** 

# 884032708/10

#### **Environmental Specifications**

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

**Operating Temperature**  $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

Acid Gas Test Method IEC 60754-2

EN50575 CPR Cable EuroClass Fire Performance No Rating

**GB 31247 Cable China Class Fire Performance** B2

GB 31247 Cable China Class Smoke Toxicity Rating t0

GB 31247 Cable China Class Droplets Rating d0

GB 31247 Cable China Class Acidity/Corrosion Rating a1

**Environmental Space** Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-1
Smoke Test Method IEC 61034-2

Packaging and Weights

Packaging Type Reel

