

Fiber OSP cable, Single Jacket/Single Armor, 432 fiber, Gel-Free, Stranded Loose Tube, Singlemode G.652.D and G.657.A1, 200um fiber, Feet jacket marking, Black jacket color

- Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection
- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber OSP cable   |
| <b>Product Series</b>        | D-LA  |
| <b>Government Funding</b>    | Build America Buy America (BABA) compliant*                         |


## General Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| <b>Armor Type</b>                   | Corrugated steel    |
| <b>Cable Type</b>                   | Stranded loose tube |
| <b>Construction Type</b>            | Armored             |
| <b>Subunit Type</b>                 | Gel-free            |
| <b>Jacket Color</b>                 | Black               |
| <b>Jacket Marking</b>               | Feet                |
| <b>Subunit, quantity</b>            | 18                  |
| <b>Fibers per Subunit, quantity</b> | 24                  |
| <b>Total Fiber Count</b>            | 432                 |

## Dimensions

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 2.5 mm   0.098 in  |
| <b>Diameter Over Jacket</b>         | 17.4 mm   0.685 in |

## Representative Image



## Material Specifications

**Jacket Material** PE

## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 261 mm   10.276 in                    |
| <b>Minimum Bend Radius, unloaded</b>     | 174 mm   6.85 in                      |
| <b>Tensile Load, long term, maximum</b>  | 800 N   179.847 lbf                   |
| <b>Tensile Load, short term, maximum</b> | 2700 N   606.984 lbf                  |
| <b>Compression</b>                       | 22 N/mm   125.623 lb/in               |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 25 cycles                             |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 4.4 N-m   38.943 in lb                |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 377 m   1,236.877 ft                  |

## Optical Specifications

# 810010237/DB | D-432-LA-8W-F24NS/200

**Fiber Type** G.652.D and G.657.A1 | OM5, LazrSPEED® wideband

## Environmental Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Installation temperature</b>      | -30 °C to +70 °C (-22 °F to +158 °F) |
| <b>Operating Temperature</b>         | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Storage Temperature</b>           | -40 °C to +75 °C (-40 °F to +167 °F) |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-87-640   EN 187105       |
| <b>Environmental Space</b>           | Aerial, lashed   Buried              |
| <b>Jacket UV Resistance</b>          | UV stabilized                        |
| <b>Water Penetration</b>             | 24 h                                 |
| <b>Water Penetration Test Method</b> | FOTP-82   IEC 60794-1 F5             |

## Environmental Test Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Cable Freeze</b>                  | -2 °C   28.4 °F                      |
| <b>Cable Freeze Test Method</b>      | FOTP-98   IEC 60794-1 F15            |
| <b>Heat Age</b>                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                       |
| <b>Low High Bend</b>                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11            |
| <b>Temperature Cycle</b>             | -40 °C to +70 °C (-40 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1              |

## Packaging and Weights

**Cable weight** 217 kg/km | 145.817 lb/kft

## Included Products

CS-8W-200UM-LT – 200 Micron Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

# CS-8W-200UM-LT

---

200 Micron Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

## Product Classification

|                     |               |
|---------------------|---------------|
| <b>Portfolio</b>    | CommScope®    |
| <b>Product Type</b> | Optical fiber |

## General Specifications

|  |  |
|--|--|
| <b>Cladding Diameter</b>                             | 125 µm                                 |
| <b>Cladding Diameter Tolerance</b>                   | ±0.7 µm                                |
| <b>Cladding Non-Circularity, maximum</b>             | 0.7 %                                  |
| <b>Coating Diameter (Colored)</b>                    | 200 µm                                 |
| <b>Coating Diameter (Uncolored)</b>                  | 190 µm                                 |
| <b>Coating Diameter Tolerance (Colored)</b>          | ±10 µm                                 |
| <b>Coating Diameter Tolerance (Uncolored)</b>        | ±10 µm                                 |
| <b>Coating/Cladding Concentricity Error, maximum</b> | 12 µm                                  |
| <b>Core/Clad Offset, maximum</b>                     | 0.5 µm                                 |
| <b>Proof Test</b>                                    | 689.476 N/mm <sup>2</sup>   100000 psi |

## Dimensions

|                            |                 |
|----------------------------|-----------------|
| <b>Fiber Curl, minimum</b> | 4 m   13.123 ft |
|----------------------------|-----------------|

## Mechanical Specifications

|   |   |
|---|---|
| <b>Macrobending, 20 mm Ø mandrel, 1 turn</b>    | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |
| <b>Macrobending, 30 mm Ø mandrel, 10 turns</b>  | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| <b>Macrobending, 60 mm Ø mandrel, 100 turns</b> | 0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm |
| <b>Coating Strip Force, maximum</b>             | 8.9 N   2.001 lbf                       |
| <b>Coating Strip Force, minimum</b>             | 0.5 N   0.112 lbf                       |
| <b>Dynamic Fatigue Parameter, minimum</b>       | 20                                      |

## Optical Specifications

|  |                    |
|--|--------------------|
| <b>Cabled Cutoff Wavelength, maximum</b> | 1260 nm            |
| <b>Point Defects, maximum</b>            | 0.05 dB            |
| <b>Zero Dispersion Slope, maximum</b>    | 0.09 ps/[km-nm-nm] |

# CS-8W-200UM-LT

---

**Zero Dispersion Wavelength, maximum** 1324 nm

**Zero Dispersion Wavelength, minimum** 1300 nm

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.25 dB/km @ 1,550 nm | 0.29 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310 nm | 0.36 dB/km @ 1,385 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550 nm

**Mode Field Diameter** 10.4  $\mu\text{m}$  @ 1,550 nm | 9.2  $\mu\text{m}$  @ 1,310 nm | 9.6  $\mu\text{m}$  @ 1,385 nm

**Mode Field Diameter Tolerance**  $\pm 0.4 \mu\text{m}$  @ 1310 nm |  $\pm 0.5 \mu\text{m}$  @ 1550 nm |  $\pm 0.6 \mu\text{m}$  @ 1385 nm

**Polarization Mode Dispersion Link Design Value, maximum** 0.04 ps/sqrt(km)

**Standards Compliance** ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

## Environmental Specifications

**Heat Aging, maximum** 0.05 dB/km @ 85 °C

**Temperature Dependence, maximum** 0.05 dB/km

**Temperature Humidity Cycling, maximum** 0.05 dB/km

**Water Immersion, maximum** 0.05 dB/km @ 23 °C

## \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity