


# 2171013-5 | TE640R-GYM2



640 Series Copper Cable, category 6A, 4 pair, UTP, CMR rated, 1000 ft, gray

## OBSOLETE

This product was discontinued on: **November 1, 2017**

### Replaced By:

884019304/10 CS44R ETL Verified Category 6A U/UTP Cable, non-plenum, gray jacket, 4 pair count, CS44R GRY C6A 4/23 U/UTP RL 1 KFT 1000 ft (305 m) length, reel

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   North America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable
<b>Product Series</b>	640 Series

## General Specifications

<b>Product Number</b>	640R
<b>ANSI/TIA Category</b>	6A
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Jacket Color</b>	Gray
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	ANSI/TIA-568.2-D   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Jacket, nominal</b>	7.569 mm   0.298 in
<b>Conductor Gauge, singles</b>	23 AWG

## Electrical Specifications

# 2171013-5 | TE640R-GYM2

---

<b>Operating Voltage, maximum</b>	80 V
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	PVC

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +75 °C (-4 °F to +167 °F)
<b>Environmental Space</b>	Non-plenum

## Packaging and Weights

<b>Cable weight</b>	58.038 kg/km   39 lb/kft
<b>Packaging Type</b>	Reel