CAP-I



CAP-L Carrier Access Point, with up to 4-Band Support for Low Power Applications

CommScope offers a range of remote carrier access points that convert the digital signal back to radio frequency (RF) for over-the-air transmission. These come in a range of transmit power and band combinations, with copper and fiber network interfaces. Carrier access points are outdoor and plenum rated.

Product Classification

Product Type Access point

Product Brand ERA®
Product Series CAP L

General Specifications

Note Detailed Product Specifications are available. Please contact your local CommScope

representative.

Power Class Low

Electrical Specifications

License Band AWS 1700 | CEL 850 | CEL 900 | DCS 1800 | EDD 800 | IMT 2100 | IMT

2600 | PCS 1900 | SMR 800 | TDD 2300 | TDD 2500 | TETRA | USA

700 | USA 750 | WCS 2300

Voltage Range -60 to -36 Vdc