

Fiber Optic Outside Plant 96 Fiber, Loose Tube, Multi-tube Cable with Corrugated Steel Armoring, OM3, HDPE

- Designed for use in backbone cabling, campus site cabling, outdoor ducts or direct burial cabling applications
- Designed with a gel filled loose tube construction to ensure protection against moisture ingress

Product Classification

Regional Availability	Asia EMEA
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LA


General Specifications

Armor Type	Corrugated steel
Cable Type	Loose tube
Subunit Type	Gel-filled
Filler, quantity	0
Jacket Color	Black
Jacket Marking	Meters
Strength Members	Central fiber reinforced polymer (FRP) rod
Fibers per Subunit, quantity	12
Total Fiber Count	96

Dimensions

Cable Length	2000 m 6,561.68 ft
Diameter Over Jacket	15.5 mm 0.61 in

Representative Image



Material Specifications

Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Tensile Load, short term, maximum 3000 N | 674.427 lbf

Cable Crush Resistance, maximum 44 N/mm | 251.246 lb/in

Flex 25 cycles

Optical Specifications

Fiber Type OM3

Optical Specifications, Wavelength Specific

Standards Compliance ANSI/TIA-568.C.3 | TIA-492CAAB (OS2)

Environmental Specifications

Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)

Packaging and Weights

Cable weight 276 kg/km | 185.463 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

