

1427592-1 | CPPR-QF-F-1U-E

Shielded Recessed Angled Panel Frame, UCP Quick-Fit, Foldable, 1U, Black



- Preferred replacement when used with MRJ21 and ACO applications

Product Classification

Regional Availability	China
Portfolio	CommScope®
Product Type	Patch panel
Product Series	SL Series

General Specifications

Application	For use with UCP Quick Fit modules
Color	Black
Modules, quantity	4
Panel Style	Angled recessed
Rack Type	EIA 19 in
Rack Units	1

Dimensions

Height	43.8 mm 1.724 in
Width	482.6 mm 19 in
Depth, with cable management	270 mm 10.63 in

Material Specifications

Material Type	Galvanised and powder-coated steel
----------------------	------------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

1427592-1 | CPPR-QF-F-1U-E

Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

