


- 1.0 GENERAL NOTES
 1.1 ALL IMPERIAL DIMENSIONS ARE IN BRACKETS [X.XX]
 1.2 MARK PART WITH IDENTIFICATION NUMBER
- 2.0 DESIGN NOTES
 2.1 DESIGNED PER CUSTOMER REQUIREMENTS
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING
 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
 5.3 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	JL1183 01SEP22	VICENTE 40155958CMO



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM NO.	PART NO.	DESCRIPTION	QTY.
1	P574-030-01	PLATE, CROSSOVER MOUNTING	1
2	VCP	CLAMP, MOUNTING	4
3	MT-381	5/8" X 12" GALV THREADED ROD	4
4	GWL-05	5/8" GALV LOCK WASHER	16
5	GWFO5A	GALV FLAT WASHER HARDENED 5/8", 1.3OD	16
6	GN-05	5/8" GALV HEX NUT	16

DENSITY	0.28	lbs/in ³
MASS	22.11	lbs
VOLUME	78.14	in ³
SURFACE AREA	554.26	in ²
DENSITY	0.0078	g/mm ³
MASS	10051.5854	grams
VOLUME	1280569.1641	mm ³
SURFACE AREA	357586.2367	mm ²
HEIGHT	213[8.4]	
LENGTH	305[12.0]	
WIDTH	213[8.4]	

COMMSCOPE, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE	X[.X] ± 6[0.25]	2 PLACE	.XX[.XXX] ± 1.50[0.06]
1 PLACE	.X[.XX] ± 3.0[0.12]	ANGLES	± 2°

FINISH: GALV A123 MATERIAL: _____

REV.	NAME	DATE	TITLE
CE	JL1183	01SEP22	UNIVERSAL CROSSOVER PLATE
RW	JL1183	09/09/2022	
AD	VCORTEZ1	09/14/2022	
RE	JL1183	09/15/2022	

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS ARE IN MILLIMETERS
 INTERPRET PER ANSI Y 14.5M-1994

SCALE: 1:1 DOCUMENT NO: **VZWSMART-MSK12**

SIZE	Auth Group	INSL	MODEL	DRAWING			SHEET	
A2	⊕	◁	VERSION	STATUS	REVISION	VERSION	STATUS	REVISION
			00	RE	A	00	RE	A

1 OF 1