

SRC9-U5A101BN001



NOVUX™ Specialty Range Closure 10, splice only, no adapters, no splitters, Stranded (4F) splice holder, Ribbon (12F) splice holder, TelSplice connector, black, 2x CR cable retention clip

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

Alternative products available:

SRC9-U5A101BN001-US NOVUX™ Specialty Range Closure 10, splice only, no adapters, no splitters, Stranded (4F) splice holder, Ribbon (12F) splice holder, TelSplice connector, black, 2x CR cable retention clip, Build America Buy America (BABA)

Product Classification

Regional Availability	Asia EMEA Latin America North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SRC10

General Specifications

Cable Capacity, Drop	2 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 2 Round 2–6.2 mm (0.08–0.24 in)
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Cable Termination Attachments, quantity	2
Closure Sealing Type	Hinged with latch
Closure Style	In-line
Color	Black
Mounting	Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included

SRC9-U5A101BN001

Network Area Type	Drop
Port, quantity	2
Splice Tray Included, quantity	1
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, maximum	4
Splicing Capacity, Single Fusion, maximum	4
Splicing Type, Supported	Single fusion
Splitter Type	No splitter

Dimensions

Width	76 mm 2.992 in
Depth	26 mm 1.024 in
Length	210 mm 8.268 in
Cable Entry Drop Port Diameter	6 mm (0.24 in) mm

Material Specifications

Material Type	Impact-resistant polymer
----------------------	--------------------------

Optical Specifications

Fiber Type	G.657.A1 G.657.A2 G.657.B3
-------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Above ground Below ground Direct burial
Qualification Standards	IEC 60529, IP68 + 1 m waterhead IEC 61753-1, category G
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton
Weight, net	0.157 kg 0.346 lb