

760256443 | TENIO-B6-START



TENIO™ B6 144f Distribution closure STARTer kit with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Suitable for all splice closure applications with a maximum capacity of 144 fibres. This basic kit contains a full set of blanking seals, one-feeder cable seal kit, cable termination units to install a loop-through feeder. Full set of splice trays for up to 144f splices. Please select distribution seal kits, CTU's and splitters from our ordering guide. This kit contains a MOBRA bracket suitable for use with PIA chambers. Fibre trays and seal kits are pre-assembled into the closure in the factory to reduce engineering time in the field.

Product Classification

Regional Availability	EMEA Latin America
Product Type	Single-ended, rectangular fiber closure
Product Brand	TENIO™
Product Series	TENIO

General Specifications

Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	6 multi-out ports (30 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	Single-ended
Color	Black
Flash Test Valve	Pre-installed
Mounting	Wall
Network Area Type	Distribution Drop
Splice Tray Included, quantity	0
Splice Tray Type Included	12-fiber, single element
Splices per Tray, quantity	12
Splicing Capacity, Single Fusion, maximum	144
Splicing Type, Supported	Single fusion

760256443 | TENIO-B6-START

Dimensions

Height	230 mm 9.055 in
Width	134 mm 5.276 in
Length	389 mm 15.315 in
Main Cable Diameter, maximum	16 mm 0.63 in

Material Specifications

Material Type	Impact-resistant polymer
----------------------	--------------------------

Environmental Specifications

Environmental Space	Below ground Buried
Qualification Standards	IEC 61300, 2 m waterhead
Water Resistance	Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton
Weight, net	1 kg 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760244933 CTU-L	-	Fiber Closure Cable Termination Unit, Large for up to 16 mm diameter cables
760250714 TENIO-MOBRA-TUBE-45x45	-	TENIO™ Mounting bracket for arm mounting
CV6797-000 TENIO-SKG3-7/10	-	TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet
CV6800-000 TENIO-B6-S12-12-V	-	TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12 heat shrink splice protectors (SMOUV 45 mm), with test valve

760256443 | TENIO-B6-START

CW8862-000
TENIO-SKG-DUMMY

- TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black



Fiber Closure Cable Termination Unit, Large for up to 16 mm diameter cables

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Cable termination bracket
Product Series	FIST-MSC FOSC-MSC TENIO

Dimensions

Single Cable Diameter, maximum	16 mm 0.63 in
---------------------------------------	-----------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Mounting bracket for arm mounting

Product Classification

Regional Availability	EMEA
Product Type	Mounting bracket
Product Series	TENIO

General Specifications

Application	For use with TENIO Fiber closures
Color	Black


Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet

Product Classification

Regional Availability	EMEA
Product Type	Cable sealing
Product Series	TENIO

General Specifications

Application	For use with TENIO Fiber closures
Cable Capacity, maximum	3
Color	Black

Dimensions

Single Cable Diameter, maximum	10 mm 0.394 in
Single Cable Diameter, minimum	7 mm 0.276 in

Packaging and Weights


Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant



CV6800-000 | TENIO-B6-S12-12-V



TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12 heat shrink splice protectors (SMOUV 45 mm), with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	EMEA Latin America
Product Type	Single-ended, rectangular fiber closure
Product Brand	TENIO™
Product Series	TENIO

General Specifications


Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	6 multi-out ports (30 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	Single-ended
Color	Black
Flash Test Valve	Pre-installed
Mounting	Wall
Network Area Type	Distribution Drop
Splice Tray Included, quantity	12
Splice Tray Type Included	12-way, heat shrink
Splices per Tray, quantity	12
Splicing Capacity, Single Fusion, maximum	144
Splicing Type, Supported	Single fusion

Dimensions

CV6800-000 | TENIO-B6-S12-12-V

Height	230 mm 9.055 in
Width	134 mm 5.276 in
Length	389 mm 15.315 in
Main Cable Diameter, maximum	16 mm 0.63 in

Ordering Tree



Material Specifications

Material Type	Impact-resistant polymer
----------------------	--------------------------

Environmental Specifications

Environmental Space	Below ground Buried
Qualification Standards	IEC 61300, 2 m waterhead
Water Resistance	Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton
Weight, net	1 kg 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

CV6800-000 | TENIO-B6-S12-12-V

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



CW8862-000 | TENIO-SKG-DUMMY



TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black

Product Classification

Regional Availability	EMEA
Product Type	Cable sealing
Product Series	TENIO

General Specifications

Application	For use with TENIO Fiber closures
Color	Black

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

