


MTC3752T3



G2 Series High Capacity Three Sector Frame Kit, 12.5 ft face, includes twelve 96 in antenna pipes plus six 96 in RRU Pipes; For patents, see www.cs-pat.com.

Product Classification

Product Type	High capacity Tower sector frame
Ordering Note	NSTD445 Compliant

General Specifications

Application	4G LTE antenna/radio mount
Mounting	Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	18
Sectors, quantity	3
Tower Taper	Non-tapered Tapered

Dimensions

Height	2,438.4 mm 96 in
Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Pipe Length	2,438.4 mm 96 in
Face Support Pipe Diameter	60.325 mm 2.375 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	50.8 mm 2 in
Pipe Outer Diameter	60.325 mm 2.375 in
Stand-off Distance	1,092.2 mm 43 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
--------------------	--

MTC3752T3

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Frame | Pipe mounts | Plain end pipes (12) | RRU Pipes (6) | Stiff arm | Tower attachment

Packaging quantity 1

Weight, net 808.755 kg | 1783 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code