

# PPLUJGFSN2PM

---

Propel ULL Singlemode Cabled Module, 6x2f duplex SN Propel module on End A to 6x24 on End B, 144 fiber LSZH Trunk, Method B Enhanced

- This component requires 6 of the 12 lanes on the Propel Panel blade
- Ultra-low loss (ULL) with Method B Enhanced polarity
- End A module can be installed from rear of panel
- Serialized QR code provides easy access to factory optical test results

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America                              |
| <b>Portfolio</b>             | SYSTIMAX®  |
| <b>Product Type</b>          | Fiber cabled module  |
| <b>Product Brand</b>         | Propel   |
| <b>Product Series</b>        | PPL  |
| <b>Ordering Note</b>         | For lengths greater than 999 ft (304 m), orders must be in meters   Maximum length is 400 meters |

## General Specifications

|                                     |                                |
|-------------------------------------|--------------------------------|
| <b>Configuration Type</b>           | PROPEL Module to MPO Connector |
| <b>Cable Color</b>                  | Yellow                         |
| <b>Cable Type</b>                   | Trunk Cable - LSZH             |
| <b>Interface, front</b>             | SN/UPC                         |
| <b>Interface Feature, front</b>     | Duplex   Shuttered             |
| <b>Interface Color, front</b>       | Blue                           |
| <b>Interface, rear</b>              | MPO-24/UPC Female              |
| <b>Interface Feature, rear</b>      | Key up/up   Unpinned           |
| <b>Module Size, end A</b>           | 24 fiber                       |
| <b>Module Size, end B</b>           | 24 fiber                       |
| <b>Module Quantity, end A</b>       | 6                              |
| <b>Module Quantity, end B</b>       | 6                              |
| <b>Polarity</b>                     | Method B Enhanced (ULL)        |
| <b>Total Fibers, quantity</b>       | 144                            |
| <b>Total Ports, quantity, front</b> | 72                             |

# PPLUJGFSN2PM

## Dimensions

|   |  |
|---|--|
| <b>Height</b>                           | 11 mm   0.433 in                                       |
| <b>Width</b>                            | 196 mm   7.717 in                                      |
| <b>Depth</b>                            | 170 mm   6.693 in                                      |
| <b>Breakout Length, end B</b>           | 12 in   120 in   33 in   36 in   48 in   60 in   72 in |
| <b>Cable Assembly Length Range (m)</b>  | 1 – 400  |
| <b>Cable Assembly Length Range (ft)</b> | 2 – 999  |

## Ordering Tree



## Optical Specifications

|                                |            |
|--------------------------------|------------|
| <b>Fiber Mode</b>              | Singlemode |
| <b>Fiber Type</b>              | OS2        |
| <b>Insertion Loss, maximum</b> | 0.6 dB     |

## Environmental Specifications

|                                |                           |
|--------------------------------|---------------------------|
| <b>Qualification Standards</b> | IEC 61753-1   TIA-568.3-D |
| <b>Safety Standard</b>         | c-UL-us                   |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

# PPLUJGFSN2PM

---

## Regulatory Compliance/Certifications

| Agency     | Classification   |
|------------|--|
| CHINA-ROHS | Below maximum concentration value  |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant  |
| UK-ROHS    | Compliant  |



## Included Products

|  |   |   |
|--|---|---|
| 760255396<br>N-144-MP-8G1-F24YL/30T/B2 | - | Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk Cable, 144 fiber with 24-fiber, 3.0 mm subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating |
|--|---|---|



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk Cable, 144 fiber with 24-fiber, 3.0mm subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber indoor cable  |
| <b>Product Series</b>        | N-MP  |

## General Specifications

|                                     |                 |
|-------------------------------------|-----------------|
| <b>Cable Type</b>                   | MPO trunk cable |
| <b>Construction Type</b>            | Non-armored     |
| <b>Subunit Type</b>                 | Gel-free        |
| <b>Jacket Color</b>                 | Yellow          |
| <b>Jacket Marking</b>               | Feet            |
| <b>Subunit, quantity</b>            | 6               |
| <b>Fibers per Subunit, quantity</b> | 24              |
| <b>Total Fiber Count</b>            | 144             |

## Dimensions

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 3 mm   0.118 in    |
| <b>Diameter Over Jacket</b>         | 12.1 mm   0.476 in |

## Representative Image



## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 182 mm   7.165 in                     |
| <b>Minimum Bend Radius, unloaded</b>     | 121 mm   4.764 in                     |
| <b>Tensile Load, long term, maximum</b>  | 400 N   89.924 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 1335 N   300.12 lbf                   |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 25 cycles                             |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 2.94 N-m   26.021 in lb               |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 288 m   944.882 ft                    |

## Optical Specifications

|                   |             |
|-------------------|-------------|
| <b>Fiber Type</b> | G.657.A2/B2 |
|-------------------|-------------|

## Environmental Specifications

|                                 |                                    |
|---------------------------------|------------------------------------|
| <b>Installation temperature</b> | 0 °C to +50 °C (+32 °F to +122 °F) |
| <b>Operating Temperature</b>    | 0 °C to +60 °C (+32 °F to +140 °F) |

# 760255396 | N-144-MP-8G1-F24YL/30T/B2

---

|   |                                       |
|---|---------------------------------------|
| <b>Storage Temperature</b>                          | -40 °C to +60 °C (-40 °F to +140 °F)  |
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-83-596   Telcordia GR-409 |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | B2ca                                  |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1a                                   |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d2                                    |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a1                                    |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)         |
| <b>Flame Test Method</b>                            | IEC 60754-2   IEC 61034-2             |

## Environmental Test Specifications

|                                      |                                    |
|--------------------------------------|------------------------------------|
| <b>Heat Age</b>                      | 0 °C to +85 °C (+32 °F to +185 °F) |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                     |
| <b>Low High Bend</b>                 | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11          |
| <b>Temperature Cycle</b>             | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 142 kg/km   95.42 lb/kft |
|---------------------|--------------------------|

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable