SFG21HD-12-4-96



G21HD High Capacity Sector Frame, 12.5 ft 2.88 in OD face pipes, includes four 96 in 2.375 OD antenna pipes

Product Classification

Product Type High capacity Tower sector frame

Product Series G2

General Specifications

Application 4G LTE antenna/radio mount

Mounting Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Patent Number Patent pending

Pipe, quantity 4

Tower Taper Non-tapered | Tapered

Dimensions

Height 2,438.4 mm | 96 in **Face Width** 3.81 m | 12.5 ft Width 3,810 mm | 150 in Pipe Length 2,438.4 mm | 96 in **Face Support Pipe Diameter** 73.025 mm | 2.875 in Mounting Diameter, maximum 218.44 mm | 8.6 in **Mounting Diameter, minimum** 38.1 mm | 1.5 in **Pipe Outer Diameter** 60.325 mm | 2.375 in Stand-off Distance 889 mm | 35 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222-G

ANDREW® an Amphenol company

SFG21HD-12-4-96

Packaging and Weights

Included Frame | Pipe mounts | Plain end pipes (3) | Stiff arm | Tower attachment

Packaging quantity 1

Weight, net 179.169 kg | 395 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

