

# SFG23-10-3-96

---



G23 High Capacity Sector Frame, 10.5 ft face, includes three 96 in pipes;  
For patents, see [www.cs-pat.com](http://www.cs-pat.com)

## OBSOLETE

This product was discontinued on: **March 22, 2023**

### Replaced By:

SFG23HDX-10-3-96

G23HDX High Capacity Sector Frame, 10.5 ft x 2.88 in OD face pipes, includes three 2.88 OD x 96 in antenna pipes

## Product Classification

**Product Type** High capacity Tower sector frame

## General Specifications

**Application** 4G LTE antenna/radio mount  
**Mounting** Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD  
**Patent Number** Patent pending  
**Pipe, quantity** 3  
**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 2,438.4 mm | 96 in  
**Face Width** 3.2 m | 10.5 ft  
**Width** 3,200.4 mm | 126 in  
**Pipe Length** 2,438.4 mm | 96 in  
**Face Support Pipe Diameter** 60.325 mm | 2.375 in  
**Mounting Diameter, maximum** 218.44 mm | 8.6 in  
**Mounting Diameter, minimum** 38.1 mm | 1.5 in  
**Pipe Outer Diameter** 60.325 mm | 2.375 in  
**Stand-off Distance** 1,226.82 mm | 48.3 in

## Material Specifications

# SFG23-10-3-96

---

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Frame | Pipe mounts | Plain end pipes (3) | Stiff arm | Tower attachment

**Packaging quantity** 1

**Weight, net** 351.534 kg | 775 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code