SA-1TR



PIM-Guard® Multifunction Adapter that threads into 3/8" & 1/2" bolts & U-bolts or snaps into 3/4" holes. One 3/4" hole for Snap-in style hangers, supporting three stacks for 4-17mm or two stacks for 26-40mm cables

- Snaps into 3/4" holes to provide 1 inch standoff
- Threads into 3/8" & 1/2" bolts & U-bolts to launch hangers
- Snaps between SnapTak hangers to provide 360 degree hanger rotation
- For patents see www.cs-pat.com

Product Classification

Product Type Adapter

Product Brand PIM-Guard®

Ordering Note ANDREW® standard product (Global)

General Specifications

Adapter Type Stand-off adapter

Color Black

Mounting 1/2 in threads | 3/4 in through hole | 3/8 in threads

Dimensions

 Height
 25.908 mm | 1.02 in

 Width
 28.956 mm | 1.14 in

Length 0.03 m | 0.1 ft

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Maximum Loading Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411,

SSH-1117

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

ANDREW® an Amphenol company

SA-1TR

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥1000 hours

Packaging and Weights

 Height, packed
 17 cm | 6.693 in

 Width, packed
 13 cm | 5.118 in

 Length, packed
 10 cm | 3.937 in

Packaging quantity 10

Weight, gross 0.15 kg | 0.331 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

