

4

3



2

1


NOTES:

- 1.0 GENERAL NOTES
 - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS.
 - 1.2 MARK PART WITH IDENTIFICATION NUMBER.
- 2.0 DESIGN NOTES
 - 2.1 WELDING WORKMANSHIP PER AWS D1.1, TABLE 6.1.
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 - 3.1 PART NUMBER FOR BARE PART IS XPU01B.
- 4.0 TEST
- 5.0 PACKAGING

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	8000030568	INITIAL RELEASE	RDLS	07/03/18
B	8000032248	UPDATED DIMENSIONS, TOL BLOCK & FORMAT	RJC	11/13/2018
C	40148276CMO	UPDATED MATERIAL TITLE BLOCK	YMENG	5/9/2022



MAT'L: FPS .375



COMMSCOPE, INC. OF NORTH CAROLINA										
TOLERANCES					SAP MATERIAL MASTER					
1 PLACE .X ± 0.06			3 PLACE .XXX ± 0.010		XPU01					
2 PLACE .XX ± 0.03			ANGLES ± 2°							
FINISH GALV A123					MATERIAL SHEET, STEEL, 0.375[9.53]THICK P/N: A1018-GR36-2					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	CE	FA	DATE	PLATE, CROSSOVER, 1.9-3.5" X 1.9-3.5" OD						
	RW	LS1146	05/31/2022							
	RV									
	AD	BCROSS	06/08/2022							
	RE	YMENG	06/10/2022							
ECN 40148276CMO				SCALE	DOCUMENT NO.					
				1:2	XPU01					
SIZE		WORK AREA	INSL	MODEL			DRAWING			SHEET 1 OF 1
C				VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	
				00	RE	A	02	RE	C	

DENSITY	0.28	lbs/in ³
MASS	4.76	lbs
VOLUME		in ³
SURFACE AREA	111.39	in ²
HEIGHT	0.375	
LENGTH	7.38	
WIDTH	7.38	

4

3

2

1