

# L6-CLAMP-4B

---



KwikClamp™ Hanger for 1-1/4 in coaxial cable, quadruple stack; includes hardware

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	KwikClamp™
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa

## General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	KwikClamp™ hanger
<b>Mounting</b>	3–25 mm flat plate   Round Member 8-25 mm

## Dimensions

<b>Maximum Stack Height</b>	1
<b>Height</b>	294 mm   11.575 in
<b>Width</b>	57 mm   2.244 in
<b>Length</b>	45 mm   1.772 in
<b>Compatible Diameter, maximum</b>	40.1 mm   1.579 in
<b>Compatible Diameter, minimum</b>	38.1 mm   1.5 in
<b>Nominal Size</b>	1-1/4 in
<b>Hanger Spacing, maximum</b>	1.83 m   6.004 ft

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

# L6-CLAMP-4B

---

## Material Specifications

**Material Type** Engineered plastic | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 12

**Weight, gross** 5.2 kg | 11.464 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power