

4


3

2

1

- 1.0 GENERAL NOTES
 - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X.X]
 - 1.2 FEATURES CRITICAL TO QUALITY ARE INDICATED IN ROUNDED BOX (X.X)
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
- 4.0 TEST
- 5.0 PACKAGING
 - 5.1 PACKAGING MUST BE AGREED TO IN WRITING BY COMMSCOPE PRIOR TO MASS-PRODUCTION APPROVAL.
 - 5.2 PARTS ARE TO BE PACKAGING IN A MANNER OT PREVENT DAMAGE DURING SHIPMENT & STORAGE.
 - 5.3 PACKAGING TO ADHERE TO ALL COMMSCOPE, LOCAL & FOREIGN (WHERE APPLICABLE) SHIPPING REQUIREMENTS.
 - 5.4 PACKAGING & PARTS TO BE FREE OF ALL CONTAMINANTS INCLUDING PAPER FROM BOX, DIRT, DUST, OILS, MOLD RELEASE, DETERGENT AND ALL OTHER FOREIGN MATERIALS.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	YMENG 13JUN23	JX1030 40171556CMO



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;
INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM	PART NO.	DESCRIPTION	QTY.	NOTE NO.
1	PGCS-1000	CLAMP,FRONT-REAR, POLYMER 4CP	2	
2	9615-15	BOLT,CARRIAGE,3/8-16,3,STL GALV	2	
3	GWL-03	3/8" GALV LOCK WASHER	2	
4	GN-03	3/8" GALV HEX NUT	2	
5	GWF-03	3/8" GALV FLAT WASHER	2	

DENSITY		lbs/in ³
MASS	0.75	lbs
VOLUME	17.03	in ³
SURFACE AREA	259.36	in ²
HEIGHT	2.65"	
LENGTH	6.55"	
WIDTH	3.85"	

COMMSCOPE, INC. OF NORTH CAROLINA													
TOLERANCES						SAP MATERIAL MASTER							
1 PLACE .X[X] ± 0.2[6.3]			3 PLACE .XXX[X] ± 0.060[1.5]			PGP-CS02							
2 PLACE .XX[X] ± 0.12[3.0]			ANGLES ± 2°										
FINISH						MATERIAL							
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994			NAME		DATE		TITLE						
			CE YMENG		13JUN23		PG PREMIUM,CBL-SUPPORT,2-HOLE						
			RW YMENG		06/13/2023								
			AD JX1030		06/18/2023								
			RE YMENG		06/19/2023								
ECN 40171556CMO			SCALE		DOCUMENT NO.		PGP-CS02						
SIZE		Auth Group		INSL		MODEL			DRAWING			SHEET	
C		 				VERSION			STATUS			1 OF 1	
						00			RE			A	

4

3

2

1