VSRA-MM-B3



Adjustable Monopole V-Stabilizer Kit 3- Sector with Ring mount - pipe not included

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 0
Sectors, quantity 3

Dimensions

Length 1,625.6 mm | 64 in

Mounting Diameter, maximum1270 mm | 50 inMounting Diameter, minimum304.8 mm | 12 inStand-off Distance1524 mm | 60 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Legs | Ring mount

Packaging quantity 1

Weight, net 65.771 kg | 145 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value



VSRA-MM-B3

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

