


# MP-PP13M-B

---



PIM Optimized Adjustable Monopole Platform Base Kit with 13ft Face - 2-7/8in OD Face Pipes & Top Rail -No Antenna Pipes Included

## Product Classification

**Product Type** Co-location platform

## General Specifications

**Mounting** Monopole, 304.8–1143 mm (12–45 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Face Width** 3.962 m | 13 ft

**Width** 3,962.4 mm | 156 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

**Mounting Diameter, maximum** 1,143 mm | 45 in

**Mounting Diameter, minimum** 304.8 mm | 12 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Platform | Rail | Ring mount

**Packaging quantity** 1

**Weight, net** 793.106 kg | 1,748.5 lb