

4



3

2

1

- 1.0 GENERAL NOTES
  - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]
  - 1.2 FOR PATENT INFO: <https://www.cs-pat.com>
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
  - 3.1 TIGHTEN ALL MOUNTING BOLTS SNUG TIGHT, DEFINED AS THE CONDITION OBTAINED WITH THE FULL EFFORT OF AN ASSEMBLER USING AN ORDINARY SPUD WRENCH TO BRING THE CONNECTING SURFACES INTO FIRM CONTACT
- 4.0 TEST
- 5.0 PACKAGING
  - 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
  - 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	AG1119 15DEC23	RW1043 40185290CMO



**BILL OF MATERIALS**  
 COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;  
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	GB0210G-00	GROUND BUS BAR, 2"X10", GALV	1	5.2

DENSITY	0.28	lbs/in <sup>3</sup>
MASS	1.12	lbs
VOLUME	3.95	in <sup>3</sup>
SURFACE AREA	46.19	in <sup>2</sup>
HEIGHT	2.0	
LENGTH	10.0	
WIDTH	0.25	

<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>										
TOLERANCES					SAP MATERIAL MASTER					
1 PLACE .X[X] ± 0.2[6.3]			3 PLACE .XXX[X] ± 0.060[1.5]		<b>UGB-0210-G</b>					
2 PLACE .XX[X] ± 0.12[3.0]			ANGLES ± 2°		FINISH STEEL, GALVANIZED					
MATERIAL SEE BOM					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994					
NAME		DATE		TITLE						
CE	LL1090	30OCT23		<b>GALV GROUND BAR: 2X10" NO/HRDWR</b>						
RW	AG1119	12/14/2023								
AD	RW1043	12/14/2023								
RE	AG1119	12/14/2023								
ECN 40185280CMO										
SCALE		DOCUMENT NO.								
<b>1:1</b>		<b>UGB-0210-G</b>								
SIZE	Auth Group	INSL	MODEL			DRAWING				SHEET
<b>C</b>			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 1	
			00	RE	A	00	RE	A		

4

3

2

1